


1. Please use the grease designated by Trident drive Harmonic Reducer installation note (MF-2 or MF-3)
2. The size with * in the figure is the reference size for installation, please follow the installation size requirements;
3. For the details of the size, please use the delivery specification drawing to confirm



MODEL	U	T	W
Wave generator-A $\phi 8$	$\phi 8H7$	$9.4^{+0.1}_{-0}$	3P9
Wave generator-A $\phi 11$	$\phi 11H7$	$12.8^{+0.1}_{-0}$	4P9
Wave generator-A $\phi 14$	$\phi 14H7$	$16.3^{+0.1}_{-0}$	5P9

NOT FOR PUBLICATION
 THE REPRODUCTION, DISTRIBUTION
 AND UTILIZATION OF THIS DOCUMENT
 AS WELL AS THE COMMUNICATION OF
 ITS CONTENTS TO OTHERS WITHOUT
 EXPRESS AUTHORIZATION IS
 PROHIBITED. OFFENDERS WILL BE
 HELD LIABLE FOR THE PAYMENT OF
 DAMAGES. ALL RIGHTS RESERVED IN
 THE EVENT OF THE GRANT OF A
 PATENT, UTILITY MODEL OR DESIGN

Title	TRIDENT DRIVE HARMONIC REDUCER
Part No	MSS-20-XX-U-I
CAD DRAWN - NOT TO BE MODIFIED BY HAND ALL DIMENSIONS IN MM	